

mini CORI-FLOW

XM12

Ex-Proof Coriolis Mass Flow Meter / Controller, 0...200 g/h



Technical specifications

Measurement & control

Type of media	liquids and gases
Flow range	liquid: 0...200 g/h (nominal flow rate: 100 g/h) gas: 0...2.66 l _n /min (N ₂) full scale (FS) value is user-configurable (5...200 g/h)
Accuracy	±0.2 % Rd (liquids) ±0.5 % Rd (gases) ±5 kg/m ³ (density)
Repeatability	±0.05 % Rd ± ½ (ZS x 100/actual flow)%
Turndown ratio	up to 1:100
Settling time (in control, typical)	1 sec. (typical)
Zero point stability (ZS)	< ±0.02 g/h
Response time (sensor)	≤ 200 msec
Operating temperature	0...55 °C
Fluid temperature	0...70 °C
Temperature sensitivity	on zero: < 0.01 g/h/°C; on span: < 0.01% Rd/°C; self heating (at zero flow): < 15 °C
Leak integrity, outboard	< 2 x 10 ⁻⁹ mbar l/s He
Max. Kv-value	2.3 x 10 ⁻³ for XM12+C2X-XC or C2X-XB (connection through the Ex-barrier) t.b.d. RC200 valve with Ex d TEIP11 I/P converter
Mounting	any position
Warm-up time	30 minutes
Storage/transport conditions	0...50 °C, max. 95 % RH (non-condensing)

Approvals

Marking	CE, UKCA, RoHS, WEEE, REACH
Ex-Protection	ATEX Zone 1, IECEx Zone 1, TIIS/JP Ex, ATEX Zone 2, IECEx Zone 2

Mechanical specs

Pressure rating (PN) - in barg	138
Ingress protection	IP66
Material wetted parts	stainless steel 316L
Housing material	aluminium AL Si7Mg03 and stainless steel 1.4301 (304) / 1.4404 (316L)
Sealing material	metal only (in fluid path)
Sensor inner diameter	single tube, DN 0.25
Process connections	1/8" OD compression type (welded) fittings; other on request
Weight	12.5 kg

Electrical properties

Power supply	15...24 Vdc ±10%
Power consumption	meter: 2.5 W typical at 24 V controller: 7 W typical at 24 V for fieldbus: add 0.9 W
Analog output	0...5 (10) Vdc or 0 (4)...20 mA (sourcing)
Analog setpoint	0...5 (10) Vdc or 0 (4)...20 mA (sinking)
Digital communication	standard: RS232; option: DeviceNet™, PROFIBUS DP, Modbus RTU, FLOW-BUS

Electrical interfaces

Actuator output	4-pin M8 (female)
Power (main connector)	Screw terminals
Function (instrument connector)	Analog, RS232
PROFIBUS DP	Screw terminals
CANopen / DeviceNet	Screw terminals
Modbus RTU/ASCII/FLOW-BUS	Screw terminals