



## Technical specifications

### Measurement & control

Accuracy	±0.5% FS
Repeatability	≤0.1% Rd
Control stability	≤±0.05% FS (typical for 1 l/min N <sub>2</sub> at specified process volume)
Response time (sensor)	2 msec
Operating temperature	-10...+70°C
Temperature sensitivity	0.1% FS/°C
Leak integrity, outboard	Elastomer sealed: < 2 x 10 <sup>-9</sup> mbar l/s He Metal sealed: < 2 x 10 <sup>-11</sup> Pa.m <sup>3</sup> /s He
Pressure range sensor	min. pressure 1.28... 64 bar, max. pressure 2... 100 bar
Max. Kv-value	6,6 x 10 <sup>-2</sup>
Mounting	Attitude sensitivity (at 90° change) < 0.3 mbar (abs./rel. sensors), < 6 mbar (dif. sensors)
Warm-up time	negligible
Storage/transport conditions	0...+50°C, max. 95% RH (non-condensing)

### Approvals

Marking	CE, RoHS, WEEE, REACH
---------	-----------------------

### Mechanical specs

Pressure rating (PN)	100
Ingress protection	IP40
Material wetted parts	stainless steel 316L or comparable
Sealing material	standard: FKM/Viton®; options: EPDM, FFKM/Kalrez®, FDA and USP Class VI approved compounds
Plunger material	standard: FFKM with PI foil; options: EPDM with PI foil, FDA and USP Class VI approved EPDM, FDA and USP Class VI approved FFKM/Kalrez®
Process connections	compression type or face seal (VCR/VCO) couplings
Weight	0.7

### Electrical properties

Power supply	+15...24 Vdc
Power consumption	3.5 W typical at 24 V for fieldbus: add 0.9 W
Analog output	0...5 (10) Vdc or 0 (4)...20 mA (sourcing)
Analog setpoint	0...5 (10) Vdc or 0 (4)...20 mA (sinking)
Digital communication	standard: RS232; options: PROFIBUS DP, CANopen®, DeviceNet™, PROFINET, EtherCAT®, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK, FLOW-BUS

### Electrical interfaces

Power (main connector)	9-pin D-sub (male)
Function (instrument connector)	RS232, Analog, RS485
PROFIBUS DP	9-pin D-sub (female)
CANopen / DeviceNet	5-pin M12A (male)
Modbus RTU/ASCII/FLOW-BUS	RJ45
Modbus TCP / EtherNet/IP / EtherCAT® / PROFINET / POWERLINK	2x RJ45