



Technical specifications

Measurement & control

Type of media	almost all gases and gas-mixes, compatible with chosen materials
Flow range	min. 0.4...20 l _n /min max. 2...200 l _n /min
Accuracy	±1.0% Rd plus ±0.5% FS (FS relates to the instrument max FS)
Repeatability	< ±0.2% FS
Turndown ratio	up to 1:100
Multi fluid capability	up to 8 calibration curves
Response time (sensor)	approx. 0.9 seconds
Operating temperature	0...+50°C
Temperature sensitivity	±0.1% Rd/°C (Air)
Leak integrity, outboard	< 2 x 10 ⁻⁸ mbar l/s He < 2 x 10 ⁻⁶ mbar l/s He (D-6471/DR3)
Pressure sensitivity	< ±0.3% Rd / bar typical (Air)
Mounting	at 90° deviation from horizontal max. error 0.2% at 1 bar typical N2
Warm-up time	30 minutes
Storage/transport conditions	0...+50°C, max. 95% RH (non-condensing)

Approvals

Mechanical specs

Pressure rating (PN) - in barg	20
Ingress protection	IP65
Material wetted parts	Aluminum EN AW-6082-T6 or stainless steel SS316, elastomer seals
Sealing material	standard: FKM/Viton® options: EPDM, FFKM/Kalrez®, FDA and USP Class VI approved compounds
Process connections	1/2" BSPF female tread (ISO1179-1); compression type or face seal (VCR/VCO) couplings
Weight	Aluminum: 1.0 kg; Stainless steel: 1.5 kg

Electrical properties

Power supply	+15...24 Vdc $\pm$ 10 %
Power consumption	1.5 W typical at 24 V for fieldbus: add + 0.9 W for display: add + 0.5 W
Analog output	0...5 (10) Vdc or 0 (4)...20 mA (sourcing)
Analog setpoint	0...5 (10) Vdc or 0 (4)...20 mA (sinking)
Digital communication	standard: RS232 options: CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus (RTU, ASCII or TCP/IP), EtherNet/IP, POWERLINK or FLOW-BUS

Electrical interfaces

Power (main connector)	8-pin DIN (male)
Function (instrument connector)	Analog, RS232, RS485
PROFIBUS DP	8-pin M12B (female)
CANopen / DeviceNet	5-pin M12A (male)
Modbus RTU/ASCII/FLOW-BUS	5-pin M12A (male)
Modbus TCP / EtherNet/IP / EtherCAT® / PROFINET / POWERLINK	2x 4 pin M12D (female)