

IN-PRESS

P-502CI

Digital Electronic Pressure Meter, Industrial Style



Technical specifications

Measurement & control

Accuracy	±0.5% FS
Repeatability	≤ 0.1% RD
Response time (sensor)	2 msec
Operating temperature	-10...+70°C; 0...+50°C for ATEX zone 2, KCs
Temperature sensitivity	0.1% FS/°C
Leak integrity, outboard	tested < 2 x 10 ⁻⁹ mbar l/s He
Pressure range sensor	min. pressure 2... 100 mbar, max. pressure 1.28... 64 bar
Warm-up time	negligible

Approvals

Marking	CE, UKCA, RoHS, WEEE, REACH
Ex-Protection	ATEX Zone 2, KCs

Mechanical specs

Pressure rating (PN) - in barg	64
Ingress protection	IP65
Material wetted parts	stainless steel 316L or comparable
Sealing material	standard: FKM/Viton®; options: EPDM, FFKM/Kalrez®, FDA and USP Class VI approved compounds
Process connections	compression type or face seal (VCR/VCO) couplings

Electrical properties

Power supply	+15...24 Vdc
Power consumption	1.5 W typical at 24 V for fieldbus: add 0.9 W
Analog output	0...5 (10) Vdc or 0 (4)...20 mA (sourcing)
Analog setpoint	0...5 (10) Vdc or 0 (4)...20 mA (sinking)
Digital communication	standard: RS232 options: PROFIBUS DP, CANopen®, DeviceNet™, PROFINET, EtherCAT®, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK, FLOW-BUS

Electrical interfaces

Power (main connector)	8-pin M12A (male)
Function (instrument connector)	RS232, Analog, RS485
PROFIBUS DP	8-pin M12B (female)
CANopen / DeviceNet	5-pin M12A (male)
Modbus RTU/ASCII/FLOW-BUS	5-pin M12A (male)
Modbus TCP / EtherNet/IP / EtherCAT® / PROFINET / POWERLINK	2x 4 pin M12D (female)