



Technical specifications

Measurement & control

Type of media	Gases
Flow range	min. 0.014...0.7 mL _N /min max. 0.06...9 mL _N /min
Accuracy	±0,8% Rd plus ±0,2% FS for F-200CI-005; ±2% FS for F-200CI-002
Repeatability	<±0.2% Rd (or <±0.04% FS whichever is greater), <±0.5% Rd for models -002- & -005-
Turndown ratio	up to 1:187.5 (1:50 in analog mode)
Multi fluid capability	Storage of max. 8 calibration curves
Settling time (in control, typical)	2 ... 4 sec.
Control stability	< ± 0.1 % FS (typical)
Operating temperature	-10...+70°C; 0...+50°C for ATEX zone 2, KCs, Class I Div 2
Temperature sensitivity	zero: < 0.05% FS/°C; span: < 0.05% Rd/°C
Leak integrity, outboard	tested < 2 x 10 ⁻⁹ mbar l/s He
Pressure sensitivity	0.1% Rd/bar typical N ₂ ; 0.01% Rd/bar typical H ₂
Max. Kv-value	6.6 x 10 ⁻²
Mounting	max. error at 90° off horizontal 0.2% at 1 bar, typical N ₂
Warm-up time	30 minutes
Storage/transport conditions	0...+50°C, max. 95% RH (non-condensing)

Approvals

Electrical safety	IEC 61010-1
Marking	CE, UKCA, RoHS, WEEE, REACH
Ex-Protection	Class I Div 2, ATEX Zone 2, KCs

Mechanical specs

Pressure rating (PN) - in barg	64
Ingress protection	IP65
Material wetted parts	stainless steel 316L or comparable
Sealing material	standard: FKM/Viton®; options: EPDM, FFKM/Kalrez®, FDA and USP Class VI approved compounds
Plunger material	standard: FFKM with PI (polyimide) foil; options: EPDM with PI foil, FDA and USP Class VI approved EPDM, FDA and USP Class VI approved FFKM/Kalrez®
Process connections	compression type or face seal (VCR/VCO) couplings
Weight	1.3 kg

Electrical properties

Power supply	+15...24 Vdc
Power consumption	3.5 W typical at 24 V for fieldbus: add 0.9 W
Analog output	0...5 (10) Vdc or 0 (4)...20 mA (sourcing)
Analog setpoint	0...5 (10) Vdc or 0 (4)...20 mA (sinking)
Digital communication	standard: RS232 options: CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK or FLOW-BUS

Electrical interfaces

Power (main connector)	8-pin DIN (male)
Function (instrument connector)	Analog, RS232, RS485
PROFIBUS DP	8-pin M12B (female)
CANopen / DeviceNet	5-pin M12A (male)
Modbus RTU/ASCII/FLOW-BUS	5-pin M12A (male)
Modbus TCP / EtherNet/IP / EtherCAT®/ PROFINET / POWERLINK	2x 4 pin M12D (female)