

## F-117CI

工業級氣體熱式質量流量計



## 技術規格

## 測量與控制

|                          |                                                            |
|--------------------------|------------------------------------------------------------|
| Type of media            | 氣體                                                         |
| 流量範圍                     | 最小值2...100 m <sup>3</sup> <sub>n</sub> /h                  |
|                          | max.20...1000 m <sup>3</sup> <sub>n</sub> /h               |
| 準確性                      | ±1% FS                                                     |
| 再現性                      | <±0.2% Rd (或 <±0.04% FS, 以較大者為準)                           |
| Turndown ratio           | 1:50                                                       |
| 多種流體功能                   | 最多可儲存8 條校準曲線                                               |
| 反應時間 (感測器)               | typical 0.5 sec                                            |
| 操作溫度                     | -10...+70°C; 0...+50°C for ATEX zone 2, KCs, Class1 Div 2  |
| 溫度敏感性                    | zero: < 0.05% FS/°C; span: < 0.05% Rd/°C                   |
| Leak integrity, outboard | 經過測試 < 2 x 10 <sup>-9</sup> mbar l/s He                    |
| 壓力敏感度                    | 0.1% Rd/bar typical N2; 0.01% Rd/bar typical H2            |
| 安裝                       | max. error at 90° off horizontal 0.2% at 1 bar, typical N2 |
| 熱機時間                     | 30分鐘                                                       |
| 儲存/運輸條件                  | 0...+50°C, max. 95% RH (non-condensing)                    |

## 審批

|         |                                 |
|---------|---------------------------------|
| 電氣安全    | IEC 61010-1                     |
| Marking | CE, UKCA, RoHS, WEEE, REACH     |
| 防爆      | Class I Div 2, ATEX Zone 2, KCs |

## 機械規格

|                       |                                                |
|-----------------------|------------------------------------------------|
| 壓力等級 (PN) - 單位: barg  | 100                                            |
| Ingress protection    | IP65                                           |
| Material wetted parts | 不銹鋼 316L 或同類材質                                 |
| 密封材質                  | 標準: FKM/Viton®; 選項: EPDM, FFKM/Kalrez®         |
| Process connections   | Flanged type, according to DIN DN80 or ANSI 3" |
| 重量                    | 26,7 kg                                        |

## 電氣特性

|       |                                                                                                                                                  |
|-------|--------------------------------------------------------------------------------------------------------------------------------------------------|
| 電源供應  | +15...24 Vdc                                                                                                                                     |
| 耗電量   | 1.5 W typical at 24 V<br>for fieldbus: add 0.9 W                                                                                                 |
| 類比輸出  | 0...5 (10) Vdc or 0 (4)...20 mA (sourcing)                                                                                                       |
| 類比設定點 | 0...5 (10) Vdc or 0 (4)...20 mA (sinking)                                                                                                        |
| 數位通訊  | standard: RS232 options: CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK or FLOW-BUS |

## 電氣介面

|                                                               |                        |
|---------------------------------------------------------------|------------------------|
| 電源(儀表接口)                                                      | 8-pin DIN (male)       |
| 通訊(儀表接口)                                                      | Analog, RS232, RS485   |
| PROFIBUS DP                                                   | 8-pin M12B (female)    |
| CANopen / DeviceNet                                           | 5-pin M12A (male)      |
| Modbus RTU/ASCII/FLOW-BUS                                     | 5-pin M12A (male)      |
| Modbus TCP / EtherNet/IP / EtherCAT®/<br>PROFINET / POWERLINK | 2x 4 pin M12D (female) |