


F-106FI

Industrial Style Thermal Mass Flow Meter for Gases



Technical specifications

Measurement & control

Type of media	Gases
Flow range	min. 14...700 m ³ _n /h max. 140...7000 m ³ _n /h
Accuracy	±1% FS plus ±1% FS per 1000 m ³ _n /h above 1100 m ³ _n /h
Repeatability	<±0.2% Rd (or <±0.04% FS whichever is greater)
Turndown ratio	1:50
Multi fluid capability	Storage of max. 8 calibration curves
Response time (sensor)	typical 0.5 sec
Operating temperature	-10...+70°C; 0...+50°C for ATEX zone 2, KCs, Class1 Div 2
Temperature sensitivity	zero: < 0.05% FS/°C; span: < 0.05% Rd/°C
Leak integrity, outboard	tested < 2 x 10 ⁻⁹ mbar l/s He
Pressure sensitivity	0.1% Rd/bar typical N2; 0.01% Rd/bar typical H2
Mounting	max. error at 90° off horizontal 0.2% at 1 bar, typical N2
Warm-up time	30 minutes
Storage/transport conditions	0...+50°C, max. 95% RH (non-condensing)

Approvals

Electrical safety	IEC 61010-1
Marking	CE, UKCA, RoHS, WEEE, REACH
Ex-Protection	Class I Div 2, ATEX Zone 2, KCs

Mechanical specs

Pressure rating (PN) - in barg	40
Ingress protection	IP65
Material wetted parts	stainless steel 316L or comparable
Sealing material	standard: FKM/Viton®; options: EPDM, FFKM/Kalrez®
Process connections	Wafer type, for mounting between flanges according to DIN DN200 or ANSI 8"
Weight	18.1 kg

Electrical properties

Power supply	+15...24 Vdc
Power consumption	1.5 W typical at 24 V for fieldbus: add 0.9 W
Analog output	0...5 (10) Vdc or 0 (4)...20 mA (sourcing)
Analog setpoint	0...5 (10) Vdc or 0 (4)...20 mA (sinking)
Digital communication	standard: RS232 options: CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK or FLOW-BUS

Electrical interfaces

Power (main connector)	8-pin DIN (male)
Function (instrument connector)	Analog, RS232, RS485
PROFIBUS DP	8-pin M12B (female)
CANopen / DeviceNet	5-pin M12A (male)
Modbus RTU/ASCII/FLOW-BUS	5-pin M12A (male)
Modbus TCP / EtherNet/IP / EtherCAT®/ PROFINET / POWERLINK	2x 4 pin M12D (female)